

## WHY PET film from silver plastics®?

- Best product presentation through high transparency
- Excellent thermoforming behaviour
- Highest protection through A/B/A film construction
- ✓ 100% recyclable mono-PET ✓
- Up to 80% recycled material use
- Also available with high barriers



## **OUR EXTRUSION**



- ✓ With silicone coating or antifog on request
- ✓ Laminating unit with corona pre-treatment
- ✓ Automated film thickness measurement
- ✓ Inline IV measuring device

## **OUR FOIL**

After intensive research and development, we were able to find a recyclable PET material for the A-layer in our film structure. We have been able to generate a recyclable PET material with optimized sealing properties.



With the help of this special mono-mixture we are able to provide our film with a safe, fast and effective sealing.

In the B-layer we offer up to 100% PCR material, 100% regrind, 100% virgin or various mixing ratios.



## **FOIL PARAMETERS**



**ROLL CORE: 3"** 76mm und **6"** 152mm

**ROLL DIAMETER:** bis zu 1050mm

FOIL THICKNESS: 250 - 1000µm

FOIL WIDTH: 500 bis 950 mm